

**Rundrohre geschweißt, W.-Nr. 1.4301 + Folie
geschliffen**

Abmessung	Korn 240/ 320	hochglanz- poliert	Abmessung	Korn 240/ 320	hochglanz- poliert	Abmessung	Korn 240/ 320	hochglanz- poliert
10,0 x 1,0	○		32,0 x 2,0	○	○	76,1 x 2,0	●	
10,0 x 1,5	○		32,0 x 3,0	○	○■	76,1 x 2,5	○	
12,0 x 1,0	○		33,7 x 1,5	○		76,1 x 3,0	○	
12,0 x 1,5	○	○	33,7 x 2,0	●	○■	76,1 x 4,0	○	
12,0 x 2,0	○		33,7 x 2,5	●		80,0 x 2,0	●	
14,0 x 1,5	○		33,7 x 3,0	○		84,0 x 2,0	○	
14,0 x 2,0	○		35,0 x 1,5	○		88,9 x 2,0	●	
15,0 x 1,0	○		35,0 x 2,0	○	○	88,9 x 3,0	○	
15,0 x 1,5	○	○	38,0 x 1,5	○	○	88,9 x 4,0	○	
15,0 x 2,0	○		38,0 x 2,0	○	○	101,6 x 2,0	●	
16,0 x 1,0	○		40,0 x 1,5	○	○	101,6 x 3,0	○	
16,0 x 1,5	○	○	40,0 x 2,0	●	○	101,6 x 4,0	○	
16,0 x 2,0	●	○	40,0 x 3,0	○		104,0 x 2,0	○	
17,2 x 1,5	○		42,4 x 1,5	○		108,0 x 2,0	○	
17,2 x 2,0	○		42,4 x 2,0	●	○	114,3 x 2,0	●	
18,0 x 1,5	○	○	42,4 x 2,5	●	○	114,3 x 3,0	○	
18,0 x 2,0	○		42,4 x 2,6			129,0 x 2,0	○	
20,0 x 1,0	○		42,4 x 3,0			139,7 x 2,0	○	
20,0 x 1,2	○	○	42,4 x 3,2			139,7 x 3,0	○	
20,0 x 1,5	○	○	44,5 x 2,0			139,7 x 4,0	○	
20,0 x 2,0	●	○	48,3 x 1,5	○		154,0 x 2,0	○	
21,3 x 2,0	●		48,3 x 2,0	●	○	154,0 x 3,0	○	
21,3 x 2,5	○		48,3 x 2,5	○	○	168,3 x 2,0	○	
22,0 x 1,5		○	48,3 x 2,6		○	168,3 x 3,0	○	
22,0 x 2,0	○	○	48,3 x 3,0	○		204,0 x 2,0	○	
25,0 x 1,0	○		48,3 x 3,2					
25,0 x 1,2	○	○	50,0 x 1,5	○				
25,0 x 1,5	○	○	50,0 x 2,0	●	○			
25,0 x 2,0	●	○■	50,8 x 1,5	○	○			
25,4 x 1,5			50,8 x 2,0		○			
26,9 x 1,5	○		51,0 x 1,2					
26,9 x 2,0	●	○■	52,0 x 1,5	○				
26,9 x 2,5	○		54,0 x 2,0	●				
28,0 x 1,5	○		60,3 x 1,5	○				
28,0 x 2,0	○	○	60,3 x 2,0	●	○			
30,0 x 1,5	○	○	60,3 x 3,0	○				
30,0 x 2,0	●	○■	60,3 x 4,0	○				
30,0 x 3,0	○		70,0 x 1,5	○				
32,0 x 1,2		○	70,0 x 2,0	○				

- Werksvorrat ungeglüht
- Werksvorrat
- Werksvorrat geglüht

Rundrohre geschweißt, Deko

Abmessung	W.-Nr. 1.4301 Dekorohr ungeglüht	W.-Nr. 1.4301 Leitungsrohr geglüht	W.-Nr. 1.4301 Leitungsrohr ungeglüht	W.-Nr. 1.4404 Leitungsrohr ungeglüht	W.-Nr. 1.4571 Leitungsrohr ungeglüht
6,0 x 1,0		○			○
8,0 x 1,0	○	○	○	○	○
8,0 x 1,5	○	○			
10,0 x 1,0	○	○	○	○	○
10,0 x 1,5	●	○	○	○	
12,0 x 1,0	●	○		○	
12,0 x 1,5	○	○		○	○
12,0 x 2,0	○	○			
14,0 x 1,0	○				
14,0 x 1,5	○				
14,0 x 2,0	○				
15,0 x 1,0	○	○			○
15,0 x 1,5	●	○			
15,0 x 2,0	○				
16,0 x 1,0	○	○			
16,0 x 1,5	○	○			
16,0 x 2,0	●				
17,2 x 1,5	○				
17,2 x 1,6		○		○	
17,2 x 2,0	●	○			
17,2 x 2,3		○	○	○	
17,2 x 2,5	○				
18,0 x 1,0	○	○			○
18,0 x 1,5	○	○	○		○
18,0 x 2,0	○				
19,0 x 1,5	○	○			
20,0 x 1,0	○	○			○
20,0 x 1,2	○	○			
20,0 x 1,5	●	○		○	○
20,0 x 2,0	○	○			○
20,0 x 2,5	○				
21,3 x 1,5	○				
21,3 x 1,6			○	○	
21,3 x 2,0	●	○		○	○
21,3 x 2,5	●				
21,3 x 2,6		○	○	○	○
21,3 x 3,0	○				

Abmessung	W.-Nr. 1.4301 Dekorrohr ungeglüht	W.-Nr. 1.4301 Leitungsrohr geglüht	W.-Nr. 1.4301 Leitungsrohr ungeglüht	W.-Nr. 1.4404 Leitungsrohr ungeglüht	W.-Nr. 1.4571 Leitungsrohr ungeglüht
22,0 x 1,0	○		○		
22,0 x 1,2	○				
22,0 x 1,5	○	○	○		
22,0 x 2,0	○	○			
23,0 x 1,5		○			
25,0 x 1,0					○
25,0 x 1,5		○	○	○	○
25,0 x 2,0	●	○	○	○	○
25,0 x 2,5	○	○			○
25,0 x 3,0	○				○
25,4 x 1,2	○		○		○
25,4 x 1,5	○		○		○
26,9 x 1,5	○				○
26,9 x 1,6	○			○	○
26,9 x 2,0	●	○	○	○	○
26,9 x 2,5					○
26,9 x 2,6			○	○	○
26,9 x 3,0					
28,0 x 1,0					
28,0 x 1,5			○		
28,0 x 2,0					
30,0 x 1,0			○		
30,0 x 1,5		○			
30,0 x 2,0	●	○		○	○
30,0 x 2,5					
30,0 x 3,0					
32,0 x 1,0					
32,0 x 1,5		○			
32,0 x 2,0		○			
32,0 x 3,0					
33,7 x 1,5					
33,7 x 1,6			○	○	○
33,7 x 2,0	●	○	○	○	
33,7 x 2,5	●				
33,7 x 2,6		○	○	○	○
33,7 x 3,0					○
33,7 x 3,2		○	○	○	○
33,7 x 3,6				○	
33,7 x 4,0					
34,0 x 1,0			○		
35,0 x 1,5	●				
35,0 x 2,0					
35,0 x 2,5					
38,0 x 1,0					
38,0 x 1,2		○			

Abmessung	W.-Nr. 1.4301 Dekorohr ungeglüht	W.-Nr. 1.4301 Leitungsrohr geglüht	W.-Nr. 1.4301 Leitungsrohr ungeglüht	W.-Nr. 1.4404 Leitungsrohr ungeglüht	W.-Nr. 1.4571 Leitungsrohr ungeglüht
38,0 x 1,5		○			○
38,0 x 2,0	●	○			
38,0 x 2,5	○				
38,0 x 3,0	○				
40,0 x 1,0	○		○	○	
40,0 x 1,5	○	○	○	○	
40,0 x 2,0	●	○			○
40,0 x 2,5	○				
40,0 x 3,0	○				
40,0 x 4,0	○				
42,4 x 1,5	○				
42,4 x 1,6			○	○	○
42,4 x 2,0	●	○	○	○	○
42,4 x 2,5	●				
42,4 x 2,6		○	○	○	○
42,4 x 3,0	○				○
42,4 x 3,2	○	○	○	○	○
42,4 x 4,0	○				
43,0 x 1,5	○				
44,5 x 1,5		○	○		
44,5 x 2,0		○	○	○	
44,5 x 2,6			○		
45,0 x 1,5	○				
45,0 x 2,0	○				
45,0 x 2,5	○				
45,0 x 3,0	○				
48,3 x 1,5	○				
48,3 x 1,6			○	○	
48,3 x 2,0	●	○	○	○	○
48,3 x 2,5	●				
48,3 x 2,6		○	○	○	○
48,3 x 3,0					○
48,3 x 3,2		○	○	○	○
48,3 x 3,6			○		
48,3 x 4,0					
50,0 x 1,0					
50,0 x 1,5		○			
50,0 x 2,0		○			
50,0 x 3,0					
50,8 x 1,2			○		
50,8 x 1,5			○		
50,8 x 2,0			○		
50,8 x 2,5			○		
51,0 x 1,5	○		○		

Abmessung	W.-Nr. 1.4301 Dekorrohr ungeglüht	W.-Nr. 1.4301 Leitungsrohr geglüht	W.-Nr. 1.4301 Leitungsrohr ungeglüht	W.-Nr. 1.4404 Leitungsrohr ungeglüht	W.-Nr. 1.4571 Leitungsrohr ungeglüht
51,0 x 2,0		○	○		
52,0 x 1,0			○		
52,0 x 1,5			○	○	
53,0 x 1,5	○		○		
54,0 x 2,0	○			○	○
57,0 x 1,5			○		
57,0 x 2,0		○	○		
57,0 x 3,0			○		
60,3 x 1,5	○				
60,3 x 1,6				○	○
60,3 x 2,0	●	○	○	○	○
60,3 x 2,5	●				
60,3 x 2,6			○		○
60,3 x 3,0	○				○
60,3 x 3,6		○	○	○	○
60,3 x 4,0	○				
63,5 x 1,5	○	○		○	
63,5 x 2,0	○				
70,0 x 1,5	○		○		
70,0 x 2,0	○		○		○
70,0 x 3,0	○		○		
76,1 x 1,5	○				
76,1 x 1,6				○	
76,1 x 2,0	●	○	○	○	○
76,1 x 2,5	○				
76,1 x 2,6			○	○	○
76,1 x 3,0	○			○	○
76,1 x 3,6			○	○	
76,1 x 4,0	○	○			
80,0 x 1,5			○		
80,0 x 2,0	○	○	○		
80,0 x 3,0	○				
80,0 x 4,0	○				
84,0 x 2,0			○	○	
85,0 x 2,0			○		
88,9 x 1,5			○		
88,9 x 1,6			○		
88,9 x 2,0	●			○	○
88,9 x 2,5	○				
88,9 x 2,6					○
88,9 x 3,0	●			○	○
88,9 x 4,0	○			○	
101,6 x 1,5	○				
101,6 x 2,0	○			○	

Abmessung	W.-Nr. 1.4301 Dekorohr ungeglüht	W.-Nr. 1.4301 Leitungsrohr geglüht	W.-Nr. 1.4301 Leitungsrohr ungeglüht	W.-Nr. 1.4404 Leitungsrohr ungeglüht	W.-Nr. 1.4571 Leitungsrohr ungeglüht
101,6 x 3,0	○				
101,6 x 4,0	○				
104,0 x 2,0	○		○	○	○
108,0 x 2,0			○		○
108,0 x 3,0			○		○
108,0 x 4,0			○		○
114,3 x 1,6				○	
114,3 x 2,0	○			○	○
114,3 x 2,5	○				
114,3 x 2,6					○
114,3 x 3,0	○			○	○
114,3 x 3,6			○		○
114,3 x 4,0	○				
129,0 x 2,0			○	○	
133,0 x 2,0			○		
133,0 x 3,0			○		
133,0 x 4,0			○		
139,7 x 1,6				○	
139,7 x 2,0			○	○	○
139,7 x 3,0			○	○	○
139,7 x 4,0			○		
154,0 x 2,0			○	○	○
154,0 x 3,0			○		
159,0 x 2,0			○		
159,0 x 3,0			○		
159,0 x 4,0			○		
168,3 x 2,0			○	○	○
168,3 x 2,5			○		
168,3 x 2,6					○
168,3 x 3,0			○		○
168,3 x 4,0			○		
204,0 x 2,0			○	○	○
219,1 x 2,0			○	○	○
219,1 x 2,9				○	
219,1 x 3,0			○		○
219,1 x 4,0			○		
254,0 x 2,0			○		○
256,0 x 4,0			○		
273,0 x 2,0				○	
273,0 x 3,0			○	○	
304,0 x 2,0			○		

- Lagervorrat
- Werksvorrat

Quadratrohre geschweisst

Abmessung	W.-Nr. 1.4301 metallblank	W.-Nr. 1.4301 geschliffen Korn 240/320	W.-Nr. 1.4571 metallblank	Abmessung	W.-Nr. 1.4301 metallblank	W.-Nr. 1.4301 geschliffen Korn 240/320	W.-Nr. 1.4571 metallblank
10 x 10 x 1,0	○	○		60 x 60 x 1,5	○		
15 x 15 x 1,0	○			60 x 60 x 2,0	●	●	○
15 x 15 x 1,2	○			60 x 60 x 2,5	○		
15 x 15 x 1,5	●	●		60 x 60 x 3,0	●	○	○
16 x 16 x 1,0	○			60 x 60 x 4,0	○	○	○
16 x 16 x 1,5	○			60 x 60 x 5,0	○		○
20 x 20 x 1,0	○	○		70 x 70 x 2,0	○		
20 x 20 x 1,2	○	○		70 x 70 x 3,0	○		
20 x 20 x 1,5	○	●	○	70 x 70 x 4,0	○		
20 x 20 x 2,0	●	●	○	70 x 70 x 5,0	○		○
25 x 25 x 1,0	○	○		80 x 80 x 2,0	○	●	○
25 x 25 x 1,2	○	○		80 x 80 x 3,0	●		○
25 x 25 x 1,5	○	○	○	80 x 80 x 4,0	○		○
25 x 25 x 2,0	●	●	○	80 x 80 x 5,0	○		○
25 x 25 x 2,5	○			80 x 80 x 6,0	○		○
30 x 30 x 1,0	○			100 x 100 x 2,0	○	●	○
30 x 30 x 1,2	○	○		100 x 100 x 3,0	●	●	○
30 x 30 x 1,5	○	○	○	100 x 100 x 4,0	○	○	○
30 x 30 x 2,0	●		○	100 x 100 x 5,0	○		○
30 x 30 x 2,5	○			100 x 100 x 6,0	○		○
30 x 30 x 3,0	●		○	120 x 120 x 3,0	○	○	○
35 x 35 x 1,5	○	○		120 x 120 x 4,0	○		○
35 x 35 x 2,0	●		○	120 x 120 x 5,0	○		○
35 x 35 x 3,0	○	○		120 x 120 x 6,0	○		○
40 x 40 x 1,2	○	○		120 x 120 x 8,0	○		
40 x 40 x 1,5	●	●	○	150 x 150 x 3,0	○		○
40 x 40 x 2,0	●	●	○	150 x 150 x 4,0	○		○
40 x 40 x 2,5	○			150 x 150 x 5,0	○		○
40 x 40 x 3,0	●	○	○	150 x 150 x 6,0	○		
40 x 40 x 4,0	●	○	○	150 x 150 x 8,0	○		
45 x 45 x 1,5	○	○		150 x 150 x 10,0	○		○
45 x 45 x 2,0	○	○		200 x 200 x 3,0	○		○
50 x 50 x 1,5	○	○		200 x 200 x 4,0	○		○
50 x 50 x 2,0	●	●	○	200 x 200 x 5,0	○		○
50 x 50 x 2,5	○			200 x 200 x 6,0	○		
50 x 50 x 3,0	●	○	○	200 x 200 x 8,0	○		
50 x 50 x 4,0	○	○	○	200 x 200 x 10,0	○		
50 x 50 x 5,0	○		○	300 x 300 x 5,0	○		

- Lagervorrat
- Werksvorrat

Quadratrohre geschweisst

Abmessung	W.-Nr. 1.4301 metallblank	W.-Nr. 1.4301 geschliffen Korn 240/320	W.-Nr. 1.4571 metallblank	Abmessung	W.-Nr. 1.4301 metallblank	W.-Nr. 1.4301 geschliffen Korn 240/320	W.-Nr. 1.4571 metallblank
20 x 10 x 1,5	○	○		60 x 40 x 2,0	●	●	○
20 x 15 x 1,5	○			60 x 40 x 2,5	○		
25 x 10 x 1,5	○			60 x 40 x 3,0	●	●	○
25 x 15 x 1,5	○	○		60 x 40 x 4,0	○		
30 x 10 x 1,5	○	○		70 x 40 x 3,0	○		
30 x 15 x 1,0	○			70 x 40 x 4,0	○		
30 x 15 x 1,5	○	○	○	80 x 10 x 1,5	○		
30 x 15 x 2,0	●	○		80 x 10 x 2,0	○		
30 x 20 x 1,5	○	○		80 x 20 x 2,0	○	○	○
30 x 20 x 2,0	○		○	80 x 30 x 2,0	○		
40 x 10 x 1,5	○			80 x 30 x 3,0	○		
40 x 10 x 2,0	●	●		80 x 40 x 2,0	●	●	○
40 x 15 x 1,5	○			80 x 40 x 3,0	○	○	○
40 x 15 x 2,0	○			80 x 40 x 4,0	○	○	○
40 x 20 x 1,2	○	○		80 x 40 x 5,0	○		
40 x 20 x 1,5	○	●	○	80 x 50 x 2,0	○		
40 x 20 x 2,0	●	●	○	80 x 50 x 3,0	○		
40 x 20 x 3,0	○			80 x 50 x 4,0	○		
40 x 27 x 1,5	○			80 x 50 x 5,0	○		
40 x 30 x 1,5	○	○		80 x 60 x 2,0	○		
40 x 30 x 2,0	●	○		80 x 60 x 3,0	○	○	○
40 x 30 x 3,0	○			80 x 60 x 4,0	○		○
50 x 10 x 1,5	○	●		80 x 60 x 5,0	○		
50 x 10 x 2,0	○	●		100 x 20 x 2,0	○	○	
50 x 20 x 1,5	○	○		100 x 40 x 2,0	○	○	○
50 x 20 x 2,0	●	○	○	100 x 40 x 3,0	○	○	○
50 x 25 x 1,5	○		○	100 x 40 x 4,0	○		○
50 x 25 x 2,0	○	○	○	100 x 40 x 5,0	○		
50 x 25 x 3,0	○			100 x 50 x 2,0	○	○	○
50 x 30 x 1,5	○			100 x 50 x 3,0	○	●	○
50 x 30 x 2,0	●	●	○	100 x 50 x 4,0	○		○
50 x 30 x 3,0	○	○	○	100 x 50 x 5,0	○		○
50 x 40 x 2,0		○		100 x 50 x 6,0	○		
50 x 40 x 3,0		○		100 x 60 x 2,0	○		
60 x 10 x 1,5				100 x 60 x 3,0	○	○	○
60 x 10 x 2,0				100 x 60 x 4,0	○		○
60 x 20 x 1,2				100 x 60 x 5,0	○		○
60 x 20 x 1,5			○	100 x 80 x 2,0	○		
60 x 20 x 2,0		○	○	100 x 80 x 3,0	○		○
60 x 30 x 1,5			○	100 x 80 x 4,0	○		
60 x 30 x 2,0	●	○	○	120 x 40 x 2,0	○		○
60 x 30 x 3,0		○	○	120 x 40 x 3,0	○		
60 x 40 x 1,5		○	○	120 x 40 x 4,0	○		

Abmessung	W.-Nr. 1.4301 metallblank	W.-Nr. 1.4301 geschliffen Korn 240/320	W.-Nr. 1.4571 metallblank	Abmessung	W.-Nr. 1.4301 metallblank	W.-Nr. 1.4301 geschliffen Korn 240/320	W.-Nr. 1.4571 metallblank
120 x 60 x 2,0	○						
120 x 60 x 3,0	○	○	○				
120 x 60 x 4,0	○		○				
120 x 60 x 5,0	○		○				
120 x 60 x 6,0	○						
120 x 80 x 2,0	○						
120 x 80 x 3,0	○	○	○				
120 x 80 x 4,0	○		○				
120 x 80 x 5,0	○						
120 x 80 x 6,0	○						
140 x 80 x 3,0	○						
140 x 80 x 4,0	○						
140 x 80 x 5,0	○						
150 x 50 x 2,0	○						
150 x 50 x 3,0	○		○				
150 x 50 x 4,0	○						
150 x 50 x 5,0	○						
150 x 80 x 3,0	○						
150 x 100 x 3,0	○		○				
150 x 100 x 4,0	○						
150 x 100 x 5,0	○		○				
150 x 100 x 6,0	○		○				
150 x 100 x 8,0	○						
160 x 80 x 3,0	○						
160 x 80 x 4,0	○						
160 x 80 x 5,0	○		○				
200 x 100 x 3,0	○						
200 x 100 x 4,0	○		○				
200 x 100 x 5,0	○		○				
200 x 100 x 6,0	○		○				
200 x 100 x 8,0	○		○				
250 x 100 x 3,0	○		○				
250 x 100 x 4,0	○						
250 x 100 x 5,0	○		○				
250 x 100 x 6,0	○						
250 x 100 x 3,0	○						
250 x 150 x 4,0	○						
250 x 150 x 5,0	○		○				
250 x 150 x 8,0	○		○				
250 x 150 x 10,0	○						
300 x 100 x 3,0	○						
300 x 100 x 4,0	○						
300 x 100 x 5,0	○		○				

- Lagervorrat
- Werksvorrat

Rohrbogen geschweisst Norm 3 s 90°, DIN 2605

W.-Nr. 1.4541

Abmessung		Abmessung		Abmessung	
20,0 x 1,50	○	35,0 x 2,00	○	60,3 x 3,20	●■
20,0 x 2,00	○	38,0 x 2,00	○	70,0 x 2,00	●■
21,3 x 2,00	●■	40,0 x 2,00	●■	76,1 x 2,00	●■
21,3 x 2,60	○	42,4 x 2,00	●■	76,1 x 3,20	○
25,0 x 2,00	○	42,4 x 2,60	●■	80,0 x 2,00	○
26,9 x 2,00	●■	42,4 x 3,20		84,0 x 2,00	○
26,9 x 2,00	○	48,3 x 2,00	●■	88,9 x 2,00	○
28,0 x 2,60	○	48,3 x 2,60	●■	88,9 x 3,20	○
30,0 x 2,00	○	48,3 x 3,20		114,3 x 2,00	○
33,7 x 2,00	●■	50,0 x 2,00		114,3 x 2,60	○
33,7 x 2,60	●■	60,3 x 2,00	●■	114,3 x 3,20	○
33,7 x 3,20	○	60,3 x 2,60	●■		

- Lagervorrat
- Werksvorrat
- Werksvorrat (W.-Nr. 1.4301)